

Price List Addendum

EFFECTIVE May 1, 2020



PL2020-GEN-ADD1

OGS-200 Steam Products

OGS-200 Rigid Coupling

STYLE 870

Refer to publication 100.02



STYLE 870 – PTFE SEAL

PIPE		Approx. Wgt. Ea. lb	COUPLING COMPLETE With PTFE Seal Assembly Price Each	SPARE PARTS PTFE Seal Assembly \$303.00
inches				
Nom. Size	Outside Dia.			
2	2.375	8.4	\$513.50	
2½	2.875	9.5	584.00	338.00
3	3.500	10.6	575.00	317.00
4	4.500	16.1	731.00	426.00
6	6.625	25.6	1083.50	677.00
8	8.625	43.2	1379.00	797.00

OGS-200 Grooved End Gate Valve

SERIES 871

Refer to publication 100.12



Size inches	Approx. Weight Each lb	Price Each
2	30.0	\$1150.50
2½	46.0	1605.50
3	50.5	1811.50
4	73.0	2481.00
6	148.0	3751.00
8	264.0	5244.50

OGS-200 Grooved End Flexible Loop for Steam

SERIES 159

Refer to publication 100.13



Size inches	Approx. Weight Each lb	Price Each
2	18.0	\$3992.50
2½	29.0	4408.50
3	43.0	5578.50
4	60.0	6966.50
6	150.0	13122.00
8	286.0	20689.00



OGS-200 Steam Products

OGS-200 Grooved End Carbon Steel Elbows

Refer to publication 100.01



No. 890C and No. 890HC



No. 811C and No. 811HC

OGS-200 GROOVED END ELBOWS – LONG RADIUS 90° ELBOW OR 45° ELBOW – CAST CARBON STEEL

Nom. Size	Long Radius 90° Elbow				45° Elbow			
	No. 890C Sch. 40		No. 890HC Sch. 80		No. 811C Sch. 40		No. 811HC Sch. 80	
	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each
inches								
2	4.0	\$186.50	4.4	\$201.00	2.7	\$146.50	3.1	\$156.00
2½	6.2	265.00	6.6	288.00	4.0	194.50	4.4	209.00
3	8.6	380.00	10.1	435.50	5.7	357.50	6.8	405.50
4	16.1	698.00	18.5	773.00	10.1	467.00	11.2	653.50
6	37.7	1736.00	47.0	2010.00	22.3	1114.00	28.0	1325.50
8	72.1	3120.00	92.8	3966.00	42.8	2093.50	55.3	2479.00

OGS-200 Grooved End Carbon Steel Tee

Refer to publication 100.01



No. 820C and No. 820HC

OGS-200 GROOVED END STANDARD TEE – CAST CARBON STEEL

Nominal	No. 820C Sch. 40		No. 820HC Sch. 80	
	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each
inches				
2	6.1	\$299.00	\$6.6	\$319.50
2½	9.5	451.00	10.8	473.00
3	14.1	630.50	16.5	707.00
4	26.2	1132.50	30.4	1256.50
6	61.3	2694.50	76.1	3309.00
8	124.5	5074.50	155.4	5977.00

OGS-200 Grooved End Carbon Steel Reducing Tee

Refer to publication 100.01



No. 825C and No. 825HC

OGS-200 GROOVED END REDUCING TEE – CAST CARBON STEEL

Nom. Size	No. 825C Sch. 40		No. 825HC Sch. 80		
	Approx. Wgt. Each lb	Price Each	Approx. Wgt. Each lb	Price Each	
inches					
Run x Branch					
2½ x 2½ x 2	6.0	\$347.50	6.5	\$360.50	
3 x 3 x 2	8.2	470.00	9.4	518.00	
	2½	8.5	496.00	9.8	532.50
4 x 4 x 2	13.2	828.00	15.0	231.50	
	2½	13.5	420.50	15.4	710.50
	3	13.8	849.50	16.0	911.50
6 x 6 x 2½	27.5	1544.50	31.0	1633.00	
	3	27.8	1537.50	34.0	1721.00
	4	28.5	1604.00	35.0	1738.00
8 x 8 x 4	47.0	2551.00	60.0	2785.00	
	6	48.5	2564.50	62.0	2824.50

OGS-200 Steam Products

OGS-200 Grooved End Carbon Steel Concentric Reducer

Refer to publication 100.01



No. 850C and No. 850HC

OGS-200 GROOVED END CONCENTRIC REDUCER – CAST CARBON STEEL

Nom. Size inches	No. 850C Sch. 40		No. 850HC Sch. 80	
	Approx. Wgt. Each lb	Price Each	Approx. Wgt. Each lb	Price Each
2½ x 2	2.4	\$146.50	2.6	\$152.00
3 x 2	2.9	175.50	3.3	184.00
	3.1	177.00	3.6	194.50
4 x 2	4.0	250.00	4.6	267.50
	5.1	250.50	4.8	273.50
	5.5	262.50	5.7	277.50
6 x 2½	12.2	289.00	13.2	334.50
	12.9	375.00	13.9	+
	7.7	392.50	9.2	465.50
8 x 4	20.4	594.50	5.5	735.00
	13.4	697.50	17.5	862.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

OGS-200 Grooved End Carbon Steel Eccentric Reducer

Refer to publication 100.01



No. 851C and No. 851HC

OGS-200 GROOVED END ECCENTRIC REDUCER – CAST CARBON STEEL

Nom. Size inches	No. 851C Sch. 40		No. 851HC Sch. 80	
	Approx. Wgt. Each lb	Price Each	Approx. Wgt. Each lb	Price Each
2½ x 2	2.4	\$184.50	2.5	\$189.50
3 x 2	2.8	200.50	3.2	213.50
	3.0	208.50	3.5	222.50
4 x 2	4.0	246.50	4.8	273.00
	4.0	251.50	4.9	278.00
	4.2	257.50	4.9	280.50
6 x 2½	12.2	447.50	13.7	506.00
	12.9	456.00	14.4	518.50
	10.0	540.00	11.8	610.50
8 x 4	20.5	736.00	26.0	798.00
	15.8	865.50	20.3	1013.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

OGS-200 Grooved End Carbon Steel Cap

Refer to publication 100.01



No. 860C and No. 860HC

OGS-200 GROOVED END CAP – CAST CARBON STEEL

Nominal inches	No. 860C Sch. 40		No. 860HC Sch. 80	
	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each
2	1.3	\$74.50	1.5	\$79.00
2½	2.0	100.50	2.2	106.50
3	2.6	134.00	3.1	147.00
4	4.4	217.00	5.1	238.50
6	9.3	457.50	11.5	530.00
8	16.8	777.00	21.4	948.50

OGS-200 Steam Products

OGS-200 Grooved End Carbon Steel Tapped Cap

NO. 860T

Refer to publication 100.01

OGS-200 GROOVED END TAPPED CAP – CAST CARBON STEEL

Nominal inches	Approx. Wgt. Ea. lb	Price Each
2	1.3	\$100.50
2½	2.0	126.00
3	2.6	162.00
4	4.4	231.50
6	9.3	420.50
8	16.8	710.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

OGS-200 Grooved End Carbon Steel Flange Adapter Nipples

Refer to publication 100.01



No. 845FC and No. 845RC



No. 846FC and No. 846RC

FLANGE ADAPTER NIPPLES – ANSI CLASS 150 AND CLASS 300 – CAST CARBON STEEL

Nom. Size inches	ANSI Class 150 Flange Adapter Nipple				ANSI Class 300 Flange Adapter Nipple			
	No. 845FC Flat Face		No. 845RC Raised Face		No. 846FC Flat Face		No. 846RC Raised Face	
	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each
2	6.6	\$126.00	6.8	\$162.00	8.2	\$408.50	8.4	\$430.00
2½	9.7	528.00	9.5	528.00	11.7	584.00	11.9	601.50
3	11.7	563.00	12.1	608.50	15.9	751.00	16.1	792.00
4	18.7	955.50	19.2	983.50	28.7	1424.00	28.7	1386.00
6	30.9	1479.50	28	1550.00	49.6	2333.00	47.8	2333.00
8	42.3	2198.00	48.5	2227.00	73.9	3408.00	72.3	3253.50

OGS-200 Steam Products

OGS-200 Grooved End Stainless Steel Elbows

Refer to publication 100.01



No. 890S



No. 811S

OGS-200 GROOVED END ELBOWS – LONG RADIUS 90° ELBOW OR 45° ELBOW – SCH. 40S TYPE 316 STAINLESS STEEL

Nom. Size inches	Long Radius 90° Elbow		45° Elbow	
	No. 890S		No. 811S	
	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each
2	4.0	+	2.7	+
2½	6.2	+	4.0	+
3	8.6	+	5.7	+
4	16.1	+	10.1	+
6	37.7	+	22.3	+
8	72.1	+	42.8	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

OGS-200 Grooved End Stainless Steel Tee

Refer to publication 100.01



No. 820S

OGS-200 GROOVED END STANDARD TEE – SCH. 40S TYPE 316 STAINLESS STEEL

Nominal inches	Tee	
	No. 820S	
	Approx. Wgt. Ea. lb	Price Each
2	6.1	+
2½	9.5	+
3	14.1	+
4	26.2	+
6	61.3	+
8	124.5	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

OGS-200 Steam Products

OGS-200 Grooved End Stainless Steel Reducing Tee

Refer to publication 100.01



No. 825S

OGS-200 GROOVED END REDUCING TEE – SCH. 40S TYPE 316 STAINLESS STEEL

Nominal inches				Reducing Tee No. 825S	
Run x Branch				Approx. Wgt. Ea. lb	Price Each
2½	x	2½	x 2	6.0	+
3	x	3	x 2	8.2	+
			x 2½	8.5	+
4	x	4	x 2	13.2	+
			x 2½	13.5	+
			x 3	13.8	+
6	x	6	x 2½	27.5	+
			x 3	27.8	+
			x 4	28.5	+
8	x	8	x 4	47.0	+
			x 6	48.5	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

OGS-200 Grooved End Stainless Steel Reducers

Refer to publication 100.01



No. 850S



No. 851S

OGS-200 GROOVED END REDUCERS

Nom. Size inches	Concentric Reducer No. 850S		Eccentric Reducer No. 851S	
	Approx. Wgt. Each lb	Price Each	Approx. Wgt. Each lb	Price Each
	2½ x 2	2.4	+	2.4
3 x 2	2.9	+	2.8	+
	3.1	+	3.0	+
4 x 2	4.0	+	4.0	+
	5.1	+	4.0	+
	5.5	+	4.2	+
6 x 2	12.2	+	12.2	+
	12.9	+	12.9	+
	7.7	+	10.0	+
8 x 4	20.4	+	20.5	+
	13.4	+	15.8	+

Other sizes available upon request. Contact Victaulic for details.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

OGS-200 Steam Products

OGS-200 Grooved End Stainless Steel Cap

Refer to publication 100.01



No. 860S

OGS-200 GROOVED END CAP – SCH. 40S TYPE 316 STAINLESS STEEL

Nominal inches	Cap No. 860S	
	Approx. Wgt. Ea. lb	Price Each
2	1.3	+
2½	2.0	+
3	2.6	+
4	4.4	+
6	9.3	+
8	16.8	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

OGS-200 Grooved End Stainless Steel Flange Adapter Nipples

Refer to publication 100.01



No. 845FS



No. 845RS

OGS-200 GROOVED END FLANGE ADAPTER NIPPLES – ANSI CLASS 150 AND CLASS 300 – SCH. 40S TYPE 316 STAINLESS STEEL

Nom. Size inches	ANSI Class 150 Flange Adapter Nipple				ANSI Class 300 Flange Adapter Nipple			
	No. 845FS Flat Face		No. 845RS Raised Face		No. 846FS Flat Face		No. 846RS Raised Face	
	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each	Approx. Wgt. Ea. lb	Price Each
2	6.6	+	6.8	+	8.2	+	8.4	+
2½	9.7	+	9.5	+	11.7	+	11.9	+
3	11.7	+	12.1	+	15.9	+	16.1	+
4	18.7	+	19.2	+	28.7	+	28.7	+
6	30.9	+	28.0	+	49.6	+	47.8	+
8	42.3	+	48.5	+	73.9	+	72.3	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

