

Price List Addendum

EFFECTIVE October 6, 2020



PL2020-GEN-ADD30

Hydraulic Control Valves

Pressure Reducing
Valve with Solenoid
Control
(400 psi)

**VICTAULIC SERIES 972-55
BERMAD MODEL BC-720-55-P**

Ductile Iron Body - Epoxy Coated
Y-Pattern

**24 VAC/Normally Closed Valve
(Solenoid Energizes to Open)**

SS 316 Tube/Fitting with SS
Control Accessories
With Mechanical Limit Switch
Pressure up to 400 psi

Nominal Size	Basic Solenoid Control Valve	
	Grooved (Standard)	
inches	Victaulic Part Code	Price Each
1½	S014972H5G	\$6303.00
2	S020972H5G	6362.00
2½	S024972H5G	6512.50
3	S030972H5G	7161.00
4	S040972H5G	7993.00
6	S060972H5G	11131.50
8	S080972H5G	23540.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

* Other finishes and valve body materials available upon request.



TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

