

Price List Addendum

EFFECTIVE September 28, 2020

V33 and V36 Dry Sprinkler Order Form



SHIP TO:

Customer Name:	DATE OF ORDER
ADDRESS	PURCHASE ORDER
CITY	SHIP VIA
STATE/PROV.	TAG
ZIP/POSTAL CODE	SIGNATURE*

* I agree to purchase the dry sprinklers specified on this order form. I understand that dry sprinklers are NON/RETURNABLE or CANCELLABLE.

Directions: Circle one of each category. DO NOT circle pipe order lengths and increments. Input appropriate length and quantity for each in the chart below. Please attach additional forms if extra ordering space is needed. Separate forms must be completed for each configuration ordered.

Class	Style	Connection	Deflector Style	Temperature	Response	K-Factor	Finish	Escutcheon Material	Pipe Order Length in inches #	Pipe Order Length in 1/8" Increments	Escutcheon Style +
5	(33) = V33	3 = 1" NPT	A = Upright	A = 135°F/57°C	Q = Quick	4 = 5.6K	1 = Plain Brass	0 = Stainless Steel	03 = 3" 15 = 15"	0 = 0"	10 = Plain Barrel
	(36) = V36	8 = 25 mm BSP H = 1" IGS without coupling L = 1" IGS with coupling	B = Pendent C = Horizontal P = Concealed	C = 155°F/68°C F = 200°F/93°C J = 286°F/141°C	S = Standard	5 = 8.0K	2 = Chrome 4 = White N = VC-250 ^ = Custom† B = Black W = Bright White		04 = 4" 16 = 16" 05 = 5" 17 = 17" 06 = 6" 18 = 18" 07 = 7" 19 = 19" 08 = 8" 20 = 20" 09 = 9" 21 = 21" 10 = 10" 22 = 22" 11 = 11" 23 = 23" 12 = 12" 24 = 24" 13 = 13" 25 = 25" 14 = 14" 26 = 26"	1 = 1/8" 2 = 1/4" 3 = 3/8" 4 = 1/2" 5 = 5/8" 6 = 3/4" 7 = 7/8"	11 = Flush 12 = Recessed 13 = Sleeve and Skirt 15 = Concealed ‡ 16 = Intermediate Std. Pendent 17 = Plain Barrel (Interchangeable Escutcheons)

Pipe order length represents the face of the tee to the bottom of the ceiling (see back for details)

† Customer must provide paint specification.

‡ Concealed coverplates are not available in Stainless Steel.

NOTE: Not all temperature ratings are listed and approved for recessed appliances. Refer to product submittal for details.

+ Escutcheon finish will be the same as sprinkler finish.

^ VC-250 coating is only available with stainless steel escutcheons

Pipe Length

Pipe order length represents the face of the tee to the bottom of the ceiling (see back for details). Pendent, Upright and Sidewall is available in 1/4" increments; Concealed is available in 1/8" increments.

Quantity	Length	Quantity	Length	Quantity	Length	Quantity	Length

NOTE: Dry sprinklers are custom made and are NON/RETURNABLE OR CANCELLABLE. Please check the above information carefully before ordering.

V40 Dry Sprinkler Order Form



SHIP TO:		DATE OF ORDER
Customer Name:		PURCHASE ORDER
ADDRESS		SHIP VIA
		TAG
CITY		SIGNATURE*
STATE/PROV.	ZIP/POSTAL CODE	

Directions: Circle one of each category. DO NOT circle pipe order lengths and increments. Input appropriate length and quantity for each in the chart below. Please attach additional forms if extra ordering space is needed. Separate forms must be completed for each configuration ordered.

Class	Style	Connection	Deflector	Temperature	Response	K-Factor	Finish	Escutcheon Material	Pipe Length inches #	Escutcheon +
5	40 = V40	3 = 1" NPT 8 = 1" BSPT H = 1" IGS without Coupling L = 1" IGS with Coupling	B = Standard Pendent	C = 155°F/68°C F = 200°F/93°C J = 286°F/141°C	S = Standard Q = Quick	6 = 11.2K	2 = Chrome 4 = White Painted N = VC-250 v	0 = Stainless Steel	120 = 12" 180 = 18" 240 = 24" 300 = 30" 360 = 36"	17 = Plain Barrel (Interchangeable Escutcheons)

Pipe order length represents the face of the tee to the bottom of the ceiling (see back for details)
 + Escutcheon finish will be the same as sprinkler finish.
 v VC-250 coating is only available with stainless steel escutcheons
 NOTE: Not all temperature ratings are listed and approved for recessed appliances. Refer to product submittal for details.

Pipe Length

Quantity	Length	Quantity	Length	Quantity	Length	Quantity	Length

NOTE: Dry sprinklers are custom made and are NON-RETURNABLE OR CANCELLABLE. Please check the above information carefully before ordering.

Dry Sprinklers

FireLock™
Model FL-QR/DRY
V3602, V3604,
V3606, V3608

**DRY TYPE
QUICK RESPONSE
1" NPT (33.7 MM) THREAD**

**Upright, K5.6 (8.1 SI) - V3602
Upright, K8.0 (11.5 SI) - V3604
Pendent, Recessed Pendent,
K5.6 (8.1 SI) - V3606
Pendent, Recessed Pendent,
K8.0 (11.5 SI) - V3608**

Refer to publication 45.01.

V3606 and V3608 available in
Flush, Recessed, Sleeve and Skirt,
and Plain Barrel (Interchangeable
Escutcheons) configurations.



Length Inches	Price Each	
	Plain Brass, Chrome, White, or Black Finishes ‡	Victaulic Proprietary Coating VC250
Min.* – 6¾	\$220.00	\$255.50
7 – 8¾	233.50	268.50
9 – 12¾	246.00	281.50
13 – 16¾	258.50	294.00
17 – 20¾	274.00	309.50
21 – 24¾	289.00	324.00
25 – 26¾	307.50	342.00
27 – 28¾	316.50	352.00
29 – 32¾	325.00	360.50
33 – 35¾	343.00	378.50
36 – 36¾	349.00	384.50
37 – 37¾	362.00	397.50

Length Inches	Price Each	
	Plain Brass, Chrome, White, or Black Finishes ‡	Victaulic Proprietary Coating VC250
38 – 38¾	\$377.00	\$412.00
39 – 39¾	391.50	427.00
40 – 40¾	406.00	441.00
41 – 41¾	419.50	455.00
42 – 42¾	433.50	468.50
43 – 43¾	447.00	482.50
44 – 44¾	461.50	496.50
45 – 45¾	474.50	510.00
46 – 46¾	487.00	522.00
47 – 47¾	501.50	536.50
48	515.00	550.00

Dry Sprinklers above 48" are not cULus Listed.

Additional lengths are possible in some configurations, please contact Victaulic for details.

Lengths 48¾" – 72" have an additional **\$177.00** LIST charge per unit.

Add **\$17.00** LIST for each additional inch on sizes 49 – 72".

* Minimum pipe order length is 4¾". Any length below 4¾" is an additional **\$74.00** LIST charge per unit.

NOTE: Sprinkler guard available, see Accessories for details.

Ceiling ring is available for purchase at an additional list price of **\$9.50**. Use part code SEE-300-0020 (Chrome) or SEE-300-0040 (White)

NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.

Recommended Wrenches: V36 Dry Open End. See Accessories for part number and price.

‡ Custom finish also available upon request, see List Adders for Sprinklers table at the beginning of this section. Allow 4-6 weeks for samples for customer finish specifications.

Dry sprinklers are non-cancellable and non-returnable.

Dry Sprinklers

FireLock™ Model FL-QR/DRY/SW V3610, V3612

**DRY TYPE
QUICK RESPONSE
1" NPT (33.7 MM) THREAD | 1"
IGS GROOVE**

**Horizontal Sidewall, Recessed
Horizontal Sidewall, K5.6 (8.1
SI) - V3610
Horizontal Sidewall, Recessed
Horizontal Sidewall, K8.0 (11.5
SI) - V3612**

Refer to publication 45.02.

V3610 and V3612 available in
Flush, Recessed, Sleeve and Skirt,
and Plain Barrel (Interchangeable
Escutcheons) configurations.



Length Inches	Price Each	
	Plain Brass, Chrome, White, or Black Finishes ‡	Victaulic Proprietary Coating VC250
Min.* – 6¾	\$236.00	\$270.50
7 – 8¾	247.00	282.50
9 – 12¾	263.00	298.00
13 – 16¾	279.50	314.50
17 – 20¾	293.00	328.00
21 – 24¾	304.50	340.00
25 – 26¾	325.00	360.50
27 – 28¾	343.50	379.00
29 – 32¾	356.00	390.50
33 – 35¾	373.00	408.50
36 – 36¾	381.00	416.50
37 – 37¾	396.00	431.00

Length Inches	Price Each	
	Plain Brass, Chrome, White, or Black Finishes ‡	Victaulic Proprietary Coating VC250
38 – 38¾	\$409.00	\$444.50
39 – 39¾	423.50	458.50
40 – 40¾	437.00	472.50
41 – 41¾	449.50	484.00
42 – 42¾	464.00	498.50
43 – 43¾	479.00	514.00
44 – 44¾	491.50	526.50
45 – 45¾	505.00	540.00
46 – 46¾	518.50	553.50
47 – 47¾	532.00	567.50
48	546.50	582.00

Dry Sprinklers above 48" are not cULus Listed.

Additional lengths are possible in some configurations, please contact Victaulic for details.

Lengths 48¾" – 72" have an additional **\$177.00** LIST charge per unit.

Add **\$17.00** LIST for each additional inch on sizes 49 – 72".

* Minimum pipe order length varies per escutcheon style. Plain barrel and flush use 2½"; sleeve & skirt and extended are 1½"; recessed is 3¼". Any lengths below minimum pipe order lengths above have an additional **\$74.00** LIST charge per unit.

NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.

Weather resistant recessed escutcheon available when used with white painted or chrome finishes.

Recommended Wrenches: V36 Dry Open End; V36 Dry Concealed/Recessed. See Accessories for part number and price.

NOTE: When applicable, VC-250 should be used in conjunction with stainless steel escutcheons.

‡ Custom finish also available upon request, see List Adders for Sprinklers table at the beginning of this section. Allow 4-6 weeks for samples for customer finish specifications.

Dry sprinklers are non-cancellable and non-returnable.

Dry Sprinklers

FireLock™
Model FL-QR/DRY/C
V3302, V3304

DRY TYPE
QUICK RESPONSE
CONCEALED PENDENT
1" NPT (33.7 MM) THREAD | 1"
IGS GROOVE

K5.6 (8.1 SI) - V3302
K8.0 (11.5 SI) - V3304
Refer to publication 45.03.



Length	Price Each §
Inches	Plain Brass, Chrome, White, or Black Finishes
Min.* – 8 ⁷ / ₈	\$297.00
9 – 12 ⁷ / ₈	308.00
13 – 16 ⁷ / ₈	332.50
17 – 20 ⁷ / ₈	354.00
21 – 24 ⁷ / ₈	368.00
25 – 26 ⁷ / ₈	373.50
27 – 28 ⁷ / ₈	382.00
29 – 32 ⁷ / ₈	394.00
33 – 35 ⁷ / ₈	405.50
36 – 36 ⁷ / ₈	446.00
37 – 37 ⁷ / ₈	460.00

Length	Price Each §
Inches	Plain Brass, Chrome, White, or Black Finishes
38 – 38 ⁷ / ₈	\$473.00
39 – 39 ⁷ / ₈	486.00
40 – 40 ⁷ / ₈	501.50
41 – 41 ⁷ / ₈	515.00
42 – 42 ⁷ / ₈	530.00
43 – 43 ⁷ / ₈	544.00
44 – 44 ⁷ / ₈	557.00
45 – 45 ⁷ / ₈	571.00
46 – 46 ⁷ / ₈	583.50
47 – 47 ⁷ / ₈	596.50
48	610.00

Concealed Dry Sprinklers above 48" are not available.

§ Price includes chrome or white painted coverplate; for custom finishes contact Victaulic for details.

* Minimum pipe order length is 4³/₄". Any length below 4³/₄" is an additional **\$74.00** LIST charge per unit.

REPLACEMENT V33 COVER PLATES (IF ADDITIONAL PLATES ARE NEEDED)

Part Code	Description	Price
S3306A0020	V33 Cover Plate Subassembly 135°F/57°C Chrome	\$16.50
S3306A0040	V33 Cover Plate Subassembly 135°F/57°C White	16.50
S3306D0020	V33 Cover Plate Subassembly 165°F/74°C Chrome	30.00
S3306D0040	V33 Cover Plate Subassembly 165°F/74°C White	30.00

Recommended Wrenches: V33 Dry Concealed/Recessed. See Accessories for part number and price.

NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.

‡ Delivery times and pricing may vary. Customer must provide paint specification.

Dry sprinklers are non-cancellable and non-returnable.

Dry Sprinklers

FireLock™
Model FL-SR/DRY
V3601, V3603,
V3605, V3607

DRY TYPE
STANDARD RESPONSE
1" NPT (33.7 MM) THREAD I
1" IGS GROOVE

Upright, K5.6 (8.1 SI) - V3601
Upright, K8.0 (11.5 SI) - V3603
Pendent, Recessed Pendent,
K5.6 (8.1 SI) - V3605
Pendent, Recessed Pendent,
K8.0 (11.5 SI) - V3607
Refer to publication 45.51.

V3605 and V3607 available in
Flush, Recessed, Sleeve and Skirt,
and Plain Barrel (Interchangeable
Escutcheons) configurations.



Length Inches	Price Each	
	Plain Brass, Chrome, White, or Black Finishes ‡	Victaulic Proprietary Coating VC250
Min.* – 6¾	\$198.00	\$233.00
7 – 8¾	211.00	246.50
9 – 12¾	224.00	259.50
13 – 16¾	242.00	277.00
17 – 20¾	253.50	288.50
21 – 24¾	275.50	311.00
25 – 26¾	283.50	319.00
27 – 28¾	291.50	326.00
29 – 32¾	302.00	337.50
33 – 35¾	320.00	354.50
36 – 36¾	329.00	363.00
37 – 37¾	343.00	378.50

Length Inches	Price Each	
	Plain Brass, Chrome, White, or Black Finishes ‡	Victaulic Proprietary Coating VC250
38 – 38¾	\$356.50	\$391.00
39 – 39¾	370.00	405.50
40 – 40¾	382.50	418.00
41 – 41¾	397.00	432.50
42 – 42¾	410.00	445.50
43 – 43¾	424.50	459.50
44 – 44¾	438.50	474.00
45 – 45¾	452.50	487.50
46 – 46¾	466.00	501.50
47 – 47¾	480.50	515.50
48	494.00	529.50

Dry Sprinklers above 48" are not cULus Listed.

Additional lengths are possible in some configurations, please contact Victaulic for details.
Lengths 48¾" – 72" have an additional **\$177.00** LIST charge per unit.

Add **\$17.00** LIST for each additional inch on sizes 49 – 72".

* Minimum pipe order length is 4¾". Any length below 4¾" is an additional **\$74.00** LIST charge per unit.

NOTE: Sprinkler guard available, see Accessories for details.

NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.

Ceiling ring is available for purchase at an additional list price of **\$9.50**. Use part code SEE-300-0020 (Chrome) or SEE-300-0040 (White)

Recommended Wrenches: V36 Dry Open End. See Accessories for part number and price.

‡ Custom finish also available upon request, see List Adders for Sprinklers table at the beginning of this section. Allow 4-6 weeks for samples for customer finish specifications.

Weather resistant stainless steel recessed escutcheon available when used with white painted or chrome finishes.

Dry sprinklers are non-cancellable and non-returnable.

Dry Sprinklers

FireLock™ Model FL-SR/DRY/SW V3609, V3611

**DRY TYPE
STANDARD RESPONSE
1" NPT (33.7 MM) THREAD I
1" IGS GROOVE**

**Horizontal Sidewall, Recessed
Horizontal Sidewall, K5.6 (8.1
SI) - V3609**

**Horizontal Sidewall, Recessed
Horizontal Sidewall, K8.0 (11.5
SI) - V3611**

Refer to publication 45.52.

V3609 and V3611 available in
Flush, Recessed, Sleeve and Skirt,
and Plain Barrel (Interchangeable
Escutcheons) configurations.



Length Inches	Price Each	
	Plain Brass, Chrome, White, or Black Finishes ‡	Victaulic Proprietary Coating VC250
Min.* – 6¾	\$191.00	\$226.50
7 – 8¾	223.00	258.00
9 – 12¾	236.00	270.50
13 – 16¾	248.00	283.50
17 – 20¾	264.50	299.00
21 – 24¾	281.50	316.00
25 – 26¾	289.00	324.00
27 – 28¾	297.00	332.50
29 – 32¾	308.00	343.00
33 – 35¾	335.50	370.50
36 – 36¾	343.50	379.00
37 – 37¾	357.50	391.50

Length Inches	Price Each	
	Plain Brass, Chrome, White, or Black Finishes ‡	Victaulic Proprietary Coating VC250
38 – 38¾	\$371.50	\$407.00
39 – 39¾	383.50	418.50
40 – 40¾	398.00	433.50
41 – 41¾	412.00	447.00
42 – 42¾	425.00	460.00
43 – 43¾	439.00	474.50
44 – 44¾	454.00	489.00
45 – 45¾	468.00	503.00
46 – 46¾	481.00	516.00
47 – 47¾	494.50	530.00
48	510.00	545.00

Dry Sprinklers above 48" are not cULus Listed.

Additional lengths are possible in some configurations, please contact Victaulic for details.

Lengths 48¾" – 72" have an additional **\$177.00** LIST charge per unit.

Add **\$17.00** LIST for each additional inch on sizes 49 – 72".

* Minimum pipe order length varies per escutcheon style. Plain barrel and flush use 2½"; sleeve & skirt and extended are 1½"; recessed is 3¾". Any lengths below minimum pipe order lengths above have an additional **\$74.00** LIST charge per unit.

NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.

Weather resistant stainless steel recessed escutcheon available when used with white painted or chrome finishes.

Recommended Wrenches: V36 Dry Open End; V36 Dry Concealed/Recessed. See Accessories for part number and price.

NOTE: When applicable, VC-250 should be used in conjunction with stainless steel escutcheons.

‡ Custom finish also available upon request, see List Adders for Sprinklers table at the beginning of this section. Allow 4-6 weeks for samples for customer finish specifications.

Dry sprinklers are non-cancellable and non-returnable.

Dry Sprinklers

FireLock™
Model FL-SR/DRY/C
V3301, V3303

DRY TYPE
STANDARD RESPONSE
CONCEALED PENDENT
1" NPT (33.7 MM) THREAD | 1"
IGS GROOVE

K5.6 (8.1 SI) - V3301
K8.0 (11.5 SI) - V3303
Refer to publication 45.53.



Length	Price Each §
Inches	Plain Brass, Chrome, White, or Black Finishes
Min.* - 8 ⁷ / ₈	\$274.50
9 - 12 ⁷ / ₈	286.00
13 - 16 ⁷ / ₈	311.50
17 - 20 ⁷ / ₈	330.50
21 - 24 ⁷ / ₈	343.00
25 - 26 ⁷ / ₈	347.50
27 - 28 ⁷ / ₈	359.50
29 - 32 ⁷ / ₈	371.50
33 - 35 ⁷ / ₈	379.00
36 - 36 ⁷ / ₈	414.50
37 - 37 ⁷ / ₈	426.00

Length	Price Each §
Inches	Plain Brass, Chrome, White, or Black Finishes
38 - 38 ⁷ / ₈	\$444.00
39 - 39 ⁷ / ₈	456.00
40 - 40 ⁷ / ₈	470.50
41 - 41 ⁷ / ₈	484.00
42 - 42 ⁷ / ₈	497.50
43 - 43 ⁷ / ₈	511.00
44 - 44 ⁷ / ₈	525.00
45 - 45 ⁷ / ₈	538.50
46 - 46 ⁷ / ₈	552.00
47 - 47 ⁷ / ₈	564.50
48	580.00

Concealed Dry Sprinklers above 48" are not available.

§ Price includes chrome or white painted coverplate; for custom finishes contact Victaulic for details.

* Minimum pipe order length is 4³/₄". Any length below 4³/₄" is an additional **\$74.00** LIST charge per unit.

REPLACEMENT V33 COVER PLATES (IF ADDITIONAL PLATES ARE NEEDED)

Part Code	Description	Price
S3306A0020	V33 Cover Plate Subassembly 135°F/57°C Chrome	\$16.50
S3306A0040	V33 Cover Plate Subassembly 135°F/57°C White	16.50
S3306D0020	V33 Cover Plate Subassembly 165°F/74°C Chrome	30.00
S3306D0040	V33 Cover Plate Subassembly 165°F/74°C White	30.00

Recommended Wrenches: V33 Dry Concealed/Recessed. See Accessories for part number and price.

NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.

‡ Delivery times and pricing may vary. Customer must provide paint specification.

Dry sprinklers are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com