

Grooved IPS Pipe Couplings

Vic-Flange Adapter for Potable Water Applications

STYLE 841

Grooved Pipe Adapters to ANSI
Class 125 and 150 Flanges
Refer to publication 06.32



STYLE 841 – GRADE “P” GASKET

PIPE inches		Approx. Wgt. Ea. lb	FLANGE ADAPTER COMPLETE † With Grade “P” Gasket Price Each	
Nom. Size	Outside Dia.		Painted	Galv.
2	2.375	3.1	\$417.00	\$504.50
2½	2.875	4.8	517.50	637.00
3	3.500	5.3	558.50	689.50
4	4.500	7.4	744.00	922.00
6	6.625	9.9	942.00	1171.50
8	8.625	16.2	1064.00	1363.00
10	10.750	24.2	1679.50	2134.00
12	12.750	46.8	2195.50	2821.50

The *Vic-Flange* adapters utilize standard ANSI 125/150 flange bolts (supplied by installer). Bolt hole pattern is standard for ANSI CL. 150 and 125 CL. flanges. Flanged Adapter Nipples are also available in ¾" / 26.9 mm and larger sizes in ANSI CL. 125, CL. 150, CL. 300 and other ANSI ratings – quoted on application.

† Surcharge for flange adapters supplied without gasket. Contact Victaulic for pricing.

NOTE: See Spare Parts Section for spare part prices.

Grooved IPS Pipe Accessories

Expansion Joint for OGS Potable Water Piping Systems



STYLE 155P

Refer to publication 09.25

STYLE 155P – EXPANSION JOINT FOR OGS POTABLE WATER PIPING SYSTEMS

Nominal Size	Painted Couplings & Uncoated SS Pipe Sections				Approx. Wgt. Ea.	COUPLING COMPLETE with Grade "P" Gasket and Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Stainless Steel Bolts & Nuts
	Movement						
	Maximum	Compressed	Neutral	Expanded		Painted Couplings and Uncoated SS Pipe Sections	
	inches				lb	Price Each	
2	0.19	8.00	8.09	8.17	4.0	\$4554.00	+
	0.38	10.25	10.43	10.61	6.3	5121.00	+
	0.57	12.50	12.78	13.05	8.6	5362.00	+
	0.76	14.75	15.12	15.49	10.9	5604.00	+
	0.95	17.00	17.47	17.93	13.2	5845.00	+
	1.14	19.25	19.81	20.37	15.5	8113.00	+
	1.33	21.50	22.16	22.81	17.7	8435.00	+
	1.52	23.75	24.50	25.25	20.0	8759.00	+
	1.71	26.00	26.85	27.69	22.3	9082.00	+
	1.90	28.25	29.19	30.13	24.6	9403.00	+
	2.09	30.50	31.54	32.57	26.9	9722.00	+
2.28	32.75	33.88	35.01	29.2	10046.00	+	
2½	0.19	8.00	8.09	8.17	5.9	5998.00	+
	0.38	10.25	10.43	10.61	8.9	7026.00	+
	0.57	12.50	12.78	13.05	12.0	7387.00	+
	0.76	14.75	15.12	15.49	15.1	7752.00	+
	0.95	17.00	17.47	17.93	18.2	8110.00	+
	1.14	19.25	19.81	20.37	21.3	8471.00	+
	1.33	21.50	22.16	22.81	24.4	8834.00	+
	1.52	23.75	24.50	25.25	27.5	10344.00	+
	1.71	26.00	26.85	27.69	30.5	10749.00	+
	1.90	28.25	29.19	30.13	33.6	11160.00	+
	2.09	30.50	31.54	32.57	36.7	11820.00	+
2.28	32.75	33.88	35.01	39.8	11551.00	+	
3	0.19	8.00	8.09	8.17	7.6	6170.00	+
	0.38	10.25	10.43	10.61	11.5	7311.00	+
	0.57	12.50	12.78	13.05	15.4	7767.00	+
	0.76	14.75	15.12	15.49	19.3	8224.00	+
	0.95	17.00	17.47	17.93	23.2	9331.00	+
	1.14	19.25	19.81	20.37	27.2	9823.00	+
	1.33	21.50	22.16	22.81	31.1	10314.00	+
	1.52	23.75	24.50	25.25	35.0	10804.00	+
	1.71	26.00	26.85	27.69	38.9	11296.00	+
	1.90	28.25	29.19	30.13	42.8	11787.00	+
	2.09	30.50	31.54	32.57	46.8	12278.00	+
2.28	32.75	33.88	35.01	50.7	12770.00	+	

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Grooved IPS Pipe Accessories

Expansion Joint for OGS Potable Water Piping Systems



STYLE 155P

Refer to publication 09.25

STYLE 155P – EXPANSION JOINT FOR OGS POTABLE WATER PIPING SYSTEMS

Nominal Size	Painted Couplings & Uncoated SS Pipe Sections				Approx. Wgt. Ea. lb	COUPLING COMPLETE with Grade "P" Gasket and Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Stainless Steel Bolts & Nuts
	Movement						
	Maximum	Compressed	Neutral	Expanded			
	inches					Painted Couplings and Uncoated SS Pipe Sections	
						Price Each	
4	0.25	11.97	12.1	12.22	3.5	\$8512.00	+
	0.5	14.35	14.6	14.85	7	9105.00	+
	0.75	16.73	17.11	17.48	10.5	9695.00	+
	1	19.11	19.61	20.11	14	10286.00	+
	1.25	21.49	22.12	22.74	17.5	10879.00	+
	1.5	23.87	24.62	25.37	21	11471.00	+
	1.75	26.25	27.13	28	24.5	12060.00	+
	2	28.63	29.63	30.63	28	12651.00	+
	2.25	31.01	32.14	33.26	31.5	13244.00	+
	2.5	33.39	34.64	35.89	35	13834.00	+
6	2.75	35.77	37.15	38.52	38.5	14425.00	+
	3	38.15	39.65	41.15	42	15018.00	+
	0.25	11.97	12.1	12.22	6.7	10582.00	+
	0.5	14.35	14.6	14.85	13.4	11926.00	+
	0.75	16.73	17.11	17.48	20.1	12733.00	+
	1	19.11	19.61	20.11	26.8	13545.00	+
	1.25	21.49	22.12	22.74	33.5	14357.00	+
	1.5	23.87	24.62	25.37	40.2	15167.00	+
	1.75	26.25	27.13	28	46.9	15981.00	+
	2	28.63	29.63	30.63	53.6	16790.00	+
8	2.25	31.01	32.14	33.26	60.3	17600.00	+
	2.5	33.39	34.64	35.89	67	18413.00	+
	2.75	35.77	37.15	38.52	73.7	19222.00	+
	3	38.15	39.65	41.15	80.4	20033.00	+
	0.25	12	12.13	12.25	12.5	12856.00	+
	0.5	14.75	15	15.25	25	14049.00	+
	0.75	17.5	17.88	18.25	37.5	15245.00	+
	1	20.25	20.75	21.25	50	16435.00	+
	1.25	23	23.63	24.25	62.5	17627.00	+
	1.5	25.75	26.5	27.25	75	19575.00	+
1.75	28.5	29.38	30.25	87.5	20815.00	+	
2	31.25	32.25	33.25	100	22053.00	+	
2.25	34	35.13	36.25	112.5	23294.00	+	
2.5	36.75	38	39.25	125	24537.00	+	
2.75	39.5	40.88	42.25	137.5	25780.00	+	
3	42.25	43.75	45.25	150	27015.00	+	

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Grooved IPS Pipe Accessories

Expansion Joint for OGS Potable Water Piping Systems



STYLE 155P

Refer to publication 09.25

STYLE 155P – EXPANSION JOINT FOR OGS POTABLE WATER PIPING SYSTEMS

Nominal Size	Painted Couplings & Uncoated SS Pipe Sections				Approx. Wgt. Ea.	COUPLING COMPLETE with Grade "P" Gasket and Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Stainless Steel Bolts & Nuts
	Movement						
	Maximum	Compressed	Neutral	Expanded	lb	Painted Couplings and Uncoated SS Pipe Sections	
	inches					Price Each	
10	0.25	16.00	16.13	16.25	82.3	\$15015.00	+
	0.50	18.75	19.00	19.25	119.9	16962.00	+
	0.75	21.50	21.88	22.25	157.4	18909.00	+
	1.00	24.25	24.75	25.25	195.0	20859.00	+
	1.25	27.00	27.63	28.25	232.6	22807.00	+
	1.50	29.75	30.50	31.25	270.2	24758.00	+
	1.75	32.50	33.38	34.25	307.8	26704.00	+
	2.00	35.25	36.25	37.25	345.3	28653.00	+
	2.25	38.00	39.13	40.25	382.9	31368.00	+
	2.50	40.75	42.00	43.25	420.5	33365.00	+
12	0.25	16.00	16.13	16.25	100.3	15495.00	+
	0.50	18.75	19.00	19.25	145.8	17679.00	+
	0.75	21.50	21.88	22.25	191.4	19861.00	+
	1.00	24.25	24.75	25.25	237.0	22046.00	+
	1.25	27.00	27.63	28.25	282.5	24230.00	+
	1.50	29.75	30.50	31.25	328.1	26412.00	+
	1.75	32.50	33.38	34.25	373.6	28596.00	+
	2.00	35.25	36.25	37.25	419.2	30778.00	+
	2.25	38.00	39.13	40.25	464.8	32962.00	+
	2.50	40.75	42.00	43.25	510.3	35146.00	+
2.75	43.50	44.88	46.25	555.9	37328.00	+	
3.00	46.25	47.75	49.25	601.4	39511.00	+	

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Style 155P Expansion Joint Configurator Painted Couplings and Uncoated Stainless Steel Pipe Sections

C A A N 155P H P Z

Class	Size in/mm	Movement	Length	Style	Finish	Gasket	Bolts and Nuts
C	E - 2/50 F - 2½/65 H - 3/80 J - 4/100 M - 6/150 O - 8/200 P - 10/250 Q - 12/300	A - 0.19 B - 0.25 C - 0.38 D - 0.50 E - 0.57 F - 0.75 G - 0.76 H - 0.95 I - 1.00 J - 1.14 K - 1.25 L - 1.33 M - 1.50 N - 1.52 O - 1.71 P - 1.75 Q - 1.90 R - 2.00 S - 2.09 T - 2.25 U - 2.28 X - 2.50 Y - 2.75 Z - 3.00	C - Compressed N - Neutral E - Expanded	155	H - Painted Blue	P - Fluoroelastomer Blend	Z - Plated X - Stainless Steel

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com