

Victaulic® FireLock™ Series FL-SA/NZ

Specific Application, Open Response

Directional Nozzle Sprinklers K1.2 (1.7), K1.8 (2.6) K2.3 (3.3), K3.2 (4.6), K4.1 (5.9), K4.9 (7.1), K5.6 (8.1), K7.2 (10.4)



1.0 PRODUCT DESCRIPTION

DIRECTIONAL SPRAY NOZZLES				
SIN	V1201-V1208	V1211-V1218	V1221-1228	V1231-V1238
ORIENTATION	VARIOUS	VARIOUS	VARIOUS	VARIOUS
K-FACTOR ¹	1.2 Imp./1.7 S.I.	1.8 Imp./2.6 S.I.	2.3 Imp./3.3 S.I.	3.2 Imp./4.6 S.I.
CONNECTION	½" NPT/15mm BSPT	½" NPT/15mm BSPT	½" NPT/15mm BSPT	½" NPT/15mm BSPT
MAX. WORKING PRESSURE	175 psi (1200 kPa)	175 psi (1200 kPa)	175 psi (1200 kPa)	175 psi (1200 kPa)

DIRECTIONAL SPRAY NOZZLES				
SIN	V1241-1248	V1251-1258	V1261-1268	V1271-1278
ORIENTATION	VARIOUS	VARIOUS	VARIOUS	VARIOUS
K-FACTOR ¹	4.1 Imp./5.9 S.I.	4.9 Imp./7.1 S.I.	5.6 Imp./8.1 S.I.	7.2 Imp./10.4 S.I.
CONNECTION	½" NPT/15mm BSPT	½" NPT/15mm BSPT	½" NPT/15mm BSPT	½" NPT/15mm BSPT
MAX. WORKING PRESSURE	175 psi (1200 kPa)	175 psi (1200 kPa)	175 psi (1200 kPa)	175 psi (1200 kPa)

AVAILABLE WRENCHES	
SPRINKLER	V27 Open End
V12	■


Min. Operating Pressure: UL/FM: 10 psi/70 kPa/7 bar (Vertically down pendent)
 UL/FM: 20 psi/140 kPa/1.4 bar (All other positions)

Deflector Angle: See tables in section 2.0

¹ For K-Factor when pressure is measured in bar, multiply S.I. units by 10.0.

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.

2.0 CERTIFICATION/LISTINGS



APPROVALS/LISTINGS					
Nominal K Factor Imperial		1.2	1.8	2.3	3.2
Nominal K Factor S.I. ²		1.7	2.6	3.3	4.6
Orientation		Various	Various	Various	Various
Agency Approvals		cULus	cULus	cULus	cULus
		FM	FM	FM	FM
SIN					
Available Deflector Angles	180°	V1201	V1211	V1221	V1231
	160°	V1202	V1212	V1222	V1232
	140°	V1203	V1213	V1223	V1233
	125°	V1204	V1214	V1224	V1234
	110°	V1205	V1215	V1225	V1235
	95°	V1206	V1216	V1226	V1236
	80°	V1207	V1217	V1227	V1237
	65°	V1208	V1218	V1228	V1238
APPROVALS/LISTINGS					
Nominal K Factor Imperial		4.1	4.9	5.6	7.2
Nominal K Factor S.I. ²		5.9	7.1	8.1	10.4
Orientation		Various	Various	Various	Various
Agency Approvals		cULus	cULus	cULus	cULus
		FM	FM	FM	FM
SIN					
Available Deflector Angles	180°	V1241	V1251	V1261	V1271
	160°	V1242	V1252	V1262	V1272
	140°	V1243	V1253	V1263	V1273
	125°	V1244	V1254	V1264	V1274
	110°	V1245	V1255	V1265	V1275
	95°	V1246	V1256	V1266	V1276
	80°	V1247	V1257	V1267	V1277
	65°	V1248	V1258	V1268	V1278

² For K-Factor when pressure is measured in Bar, multiply S.I. units by 10.

NOTE

- Listings and approval as of printing.
- Victaulic V12 Spray Nozzles are open type spray nozzles designed for directional spray applications in fixed fire protection systems. They have an open design only (non-automatic) with a deflector that discharges a solid uniform cone spray of low- to medium- velocity water droplets. Victaulic V12 Spray Nozzles are available in multiple orifice sizes and spray angles to meet various design application requirements.
- For nozzles having nominal U.S. K-Factors of 1.2, 1.8, 2.3, and 3.2, a bushing is used, whereas nozzles with K-Factors of 4.1, 4.9, 5.6, and 7.2 are machined orifices.

3.0 SPECIFICATIONS – MATERIAL

Deflector: Bronze

Load Screw: Stainless steel

Frame: Brass

Bushing: Brass

Splitter: Brass

Installation Wrench: Ductile iron


Sprinkler Frame Finishes:

- Plain brass
- VC-250³

³ UL Listed and FM Approved for corrosion resistance.


NOTE

- For cabinets and other accessories refer to separate sheet.
- Bushing: V1201 – V1238 ONLY



V12

4.0 DIMENSIONS



V2601, V2603

5.0 PERFORMANCE

Sprinkler is to be installed as per NFPA, FM Datasheets, or any local standards.




FIGURE 1: K FACTOR DISCHARGE CURVES

5.0 PERFORMANCE (CONTINUED)




FIGURE 2: DESIGN SPRAY PROFILES (ALL K FACTORS)




FIGURE 3: SPRAY COVERAGE VARIABLES

NOTES

- K-factors have tolerances of +/- 0.2 GPM/ $\sqrt{\text{PSI}}$ (0.2 LPM/ $\sqrt{\text{kPa}}$) from nominal. The design spray profile is the included angle of discharge for each nozzle.
- Figure 2 illustrates the radial distance at various heights based upon testing in the pendent position at 10 psi, 20 psi, and 60 psi / 69 kPa, 138 kPa, and 414 kPa discharge pressure (see Figure 3, Variable C).
- For FM only installations, use a recommended tolerance of +/- 2 ft [0.6 m] from nominal for the radial distances shown (x-axis) in Figure 2 for all fixed angle orientations. Use a recommended spray profile angle tolerance of +/- 5° in the pendent position (vertically downward) and +/-10° in all other fixed angle orientations.
- For UL/NFPA only installations, use a recommended tolerance of +/-15% from nominal for the radial distances shown (x-axis) in Figure 2 for all fixed angle orientations.
- Spray profiles will tend to decrease (or pull inward) with an increase in pressure. All test data was obtained in a stagnant air environment.
- See Exposure Protection Tables for fixed angle orientation and maximum axial distance from the plane of protection for each model.
- A system strainer is needed if orifice diameter is less than 3/8"/9.4 mm, which includes V12 spray nozzles of K-Factors 3.2, 2.3, 1.8 and 1.2.

Maximum Axial Distance For 65° Spray Angle in Imperial								
Fixed Angle	K-Factor							
	1.2	1.8	2.3	3.2	4.1	4.9	5.6	7.2
0°	14-9	15-0	15-0	15-3	15-3	15-6	15-9	16-0
30°	9-9	9-9	10-0	10-3	10-6	10-9	11-0	11-6
45°	8-0	8-0	8-6	9-0	9-3	9-6	9-9	10-3
60°	7-0	7-3	7-9	8-3	8-6	8-6	8-9	9-6
90°	6-6	6-9	7-0	7-6	7-9	8-0	8-0	8-6
120°	6-3	6-6	6-9	7-3	7-3	7-6	7-6	7-9
135°	5-9	6-0	6-3	6-6	6-9	6-9	7-0	7-6
150°	5-6	5-9	6-0	6-0	6-6	6-9	6-9	7-3
180°	5-0	5-0	5-3	5-6	6-0	6-3	6-6	6-9

Maximum Axial Distance For 125° Spray Angle in Imperial								
Fixed Angle	K-Factor							
	1.2	1.8	2.3	3.2	4.1	4.9	5.6	7.2
0°	7-9	7-9	7-9	8-0	8-3	8-3	8-6	8-9
30°	5-0	5-3	5-6	5-9	6-9	7-3	7-9	7-9
45°	4-3	4-6	4-9	5-0	6-0	6-3	6-6	7-0
60°	3-6	3-9	4-0	4-3	5-3	5-6	5-9	6-3
90°	3-0	3-3	3-6	3-6	4-3	4-6	4-9	5-3
120°	2-0	2-0	2-6	3-3	3-9	3-9	3-9	4-3
135°	1-9	1-9	2-3	3-0	3-6	3-6	3-6	3-9
150°	1-6	1-9	2-3	2-6	3-0	3-3	3-3	3-6
180°	1-3	1-6	2-0	2-6	2-9	2-9	3-0	3-3

5.0 PERFORMANCE (CONTINUED)

Maximum Axial Distance For 80° Spray Angle in Imperial								
Fixed Angle	K-Factor							
	1.2	1.8	2.3	3.2	4.1	4.9	5.6	7.2
0°	14-9	15-0	15-0	15-3	15-3	15-6	15-9	16-0
30°	9-6	9-9	10-3	10-6	10-9	10-9	11-0	11-3
45°	7-6	7-9	8-3	8-6	9-0	9-0	9-3	9-9
60°	6-3	6-6	6-9	7-0	7-6	7-6	8-3	8-9
90°	5-9	6-3	6-6	6-9	7-3	7-3	7-6	7-9
120°	5-3	5-6	5-9	6-0	6-3	6-3	6-6	7-0
135°	4-9	5-3	5-6	5-9	6-0	6-0	6-3	6-6
150°	4-3	4-6	4-9	5-6	5-9	5-9	6-0	6-0
180°	4-0	4-3	4-6	5-3	5-6	5-6	5-9	5-9

Maximum Axial Distance For 140° Spray Angle in Imperial								
Fixed Angle	K-Factor							
	1.2	1.8	2.3	3.2	4.1	4.9	5.6	7.2
0°	6-3	6-3	6-3	6-6	6-6	6-6	6-9	6-9
30°	3-9	3-9	4-3	4-9	5-3	5-3	5-6	5-9
45°	3-0	3-3	3-6	4-3	4-9	5-0	5-0	5-3
60°	2-3	2-6	2-9	3-9	4-3	4-3	4-6	4-9
90°	2-0	2-0	2-6	3-0	3-6	3-9	3-9	4-0
120°	1-9	1-9	2-3	2-6	2-9	2-9	3-0	3-6
135°	1-6	1-6	1-9	2-3	2-6	2-6	2-9	3-0
150°	1-3	1-3	1-6	1-9	2-0	2-0	2-3	2-6
180°	1-0	1-0	1-3	1-6	1-9	1-9	2-0	2-3

Maximum Axial Distance For 95° Spray Angle in Imperial								
Fixed Angle	K-Factor							
	1.2	1.8	2.3	3.2	4.1	4.9	5.6	7.2
0°	14-9	15-0	15-0	15-3	15-3	15-6	15-9	16-0
30°	8-3	8-6	9-3	9-6	10-3	10-6	10-6	11-3
45°	7-0	7-0	7-3	7-6	8-6	8-9	9-0	9-9
60°	5-3	5-6	5-9	6-6	6-9	7-0	7-6	8-6
90°	4-6	4-9	5-6	5-9	6-0	6-0	6-3	6-9
120°	4-0	4-3	4-6	5-0	5-3	5-6	5-6	5-9
135°	3-9	3-9	4-3	4-9	5-0	5-3	5-3	5-6
150°	3-3	3-6	3-6	4-6	4-9	4-9	5-0	5-3
180°	3-0	3-3	3-3	4-0	4-3	4-3	4-6	4-9

Maximum Axial Distance For 160° Spray Angle in Imperial								
Fixed Angle	K-Factor							
	1.2	1.8	2.3	3.2	4.1	4.9	5.6	7.2
0°	4-9	4-9	4-9	5-0	5-0	5-0	5-3	5-3
30°	3-9	3-9	4-0	4-0	4-6	4-6	4-6	4-9
45°	3-0	3-0	3-6	3-9	4-0	4-0	4-0	4-3
60°	2-0	2-0	2-3	2-6	3-3	3-3	3-6	3-6
90°	1-0	1-3	1-9	2-0	2-6	2-6	2-6	2-9
120°	NR	1-0	1-6	1-9	2-0	2-3	2-3	2-6
135°	NR	NR	1-0	1-6	1-9	1-9	1-9	2-0
150°	NR	NR	NR	1-0	1-3	1-3	1-6	1-9
180°	NR	NR	NR	1-0	1-0	1-0	1-3	1-6

Maximum Axial Distance For 110° Spray Angle in Imperial								
Fixed Angle	K-Factor							
	1.2	1.8	2.3	3.2	4.1	4.9	5.6	7.2
0°	9-6	9-9	9-9	10-0	10-3	10-6	10-9	11-0
30°	6-6	6-9	7-3	8-0	8-6	8-9	9-0	9-6
45°	5-6	6-0	6-9	7-0	7-6	7-9	8-3	8-6
60°	4-9	5-0	5-6	5-9	6-3	6-9	7-3	7-9
90°	3-9	4-0	4-6	4-9	5-3	5-6	5-9	6-3
120°	3-3	3-6	4-0	4-3	4-6	4-6	4-9	5-3
135°	2-9	3-0	3-6	4-0	4-3	4-3	4-6	4-9
150°	2-6	2-9	3-3	3-6	4-0	4-3	4-3	4-6
180°	2-3	2-6	3-0	3-3	3-6	3-9	4-0	4-3

Maximum Axial Distance For 180° Spray Angle in Imperial								
Fixed Angle	K-Factor							
	1.2	1.8	2.3	3.2	4.1	4.9	5.6	7.2
0°	3-3	3-3	3-3	3-6	3-6	3-9	3-9	3-9
30°	2-3	2-3	2-6	2-9	2-9	3-3	3-3	3-3
45°	2-0	2-0	2-3	2-6	2-6	3-0	3-0	3-0
60°	1-6	1-6	1-9	2-0	2-0	2-3	2-6	2-6
90°	NR	NR	1-0	1-0	1-0	1-9	2-0	2-3
120°	NR	NR	1-0	1-0	1-0	1-6	1-6	1-9
135°	NR	NR	NR	1-0	1-0	1-3	1-3	1-6
150°	NR	NR	NR	NR	1-0	1-0	1-3	1-3
180°	NR	NR	NR	NR	NR	1-0	1-0	1-0




FIGURE 4: K FACTOR DISCHARGE CURVES (METRIC)

5.0 PERFORMANCE (CONTINUED)




FIGURE 5: DESIGN SPRAY PROFILES (METRIC, ALL K FACTORS)

Maximum Axial Distance For 65° Spray Angle in Metric								
Fixed Angle	K-Factor							
	1.7	2.6	3.3	4.6	5.9	7.1	8.1	10.4
0°	4.5	4.6	4.60	4.60	4.60	4.70	4.80	4.90
30°	3.0	3.0	3.00	3.10	3.20	3.40	3.40	3.50
45°	2.4	2.4	2.60	2.70	2.80	3.00	3.00	3.10
60°	2.1	2.2	2.40	2.50	2.60	2.70	2.70	2.90
90°	2.0	2.1	2.10	2.30	2.40	2.40	2.40	2.60
120°	1.9	2.0	2.10	2.20	2.20	2.30	2.30	2.40
135°	1.8	1.8	1.90	2.00	2.10	2.10	2.10	2.30
150°	1.7	1.8	1.80	1.80	2.00	2.10	2.10	2.20
180°	1.5	1.5	1.60	1.70	1.80	2.00	2.00	2.10

Maximum Axial Distance For 125° Spray Angle in Metric								
Fixed Angle	K-Factor							
	1.7	2.6	3.3	4.6	5.9	7.1	8.1	10.4
0°	2.4	2.4	2.4	2.4	2.5	2.5	2.6	2.7
30°	1.5	1.6	1.7	1.8	2.1	2.2	2.4	2.4
45°	1.3	1.4	1.4	1.5	1.8	1.9	2.0	2.1
60°	1.1	1.1	1.2	1.3	1.6	1.7	1.8	1.9
90°	0.9	1.0	1.1	1.1	1.3	1.4	1.4	1.6
120°	0.6	0.6	0.8	1.0	1.1	1.1	1.1	1.3
135°	0.5	0.5	0.7	0.9	1.1	1.1	1.1	1.1
150°	0.5	0.5	0.7	0.8	0.9	1.0	1.0	1.1
180°	0.4	0.5	0.6	0.8	0.8	0.8	0.9	1.0

Maximum Axial Distance For 80° Spray Angle in Metric								
Fixed Angle	K-Factor							
	1.7	2.6	3.3	4.6	5.9	7.1	8.1	10.4
0°	4.5	4.6	4.6	4.6	4.6	4.8	4.8	4.9
30°	2.9	3.0	3.1	3.2	3.3	3.3	3.4	3.4
45°	2.3	2.4	2.5	2.6	2.7	2.7	2.8	3.0
60°	1.9	2.0	2.1	2.1	2.2	2.3	2.5	2.7
90°	1.8	1.9	2.0	2.1	2.1	2.2	2.3	2.4
120°	1.6	1.7	1.8	1.8	1.9	1.9	2.0	2.1
135°	1.4	1.6	1.7	1.8	1.8	1.8	1.9	2.0
150°	1.3	1.4	1.4	1.7	1.8	1.8	1.8	1.8
180°	1.2	1.3	1.4	1.6	1.7	1.7	1.8	1.8

Maximum Axial Distance For 140° Spray Angle in Metric								
Fixed Angle	K-Factor							
	1.7	2.6	3.3	4.6	5.9	7.1	8.1	10.4
0°	1.9	1.9	1.9	2.0	2.0	2.0	2.1	2.1
30°	1.1	1.1	1.3	1.4	1.6	1.6	1.7	1.8
45°	0.9	1.0	1.1	1.3	1.4	1.5	1.5	1.6
60°	0.7	0.8	0.8	1.1	1.3	1.3	1.4	1.4
90°	0.6	0.6	0.8	0.9	1.1	1.1	1.1	1.2
120°	0.5	0.5	0.7	0.8	0.8	0.8	0.9	1.1
135°	0.5	0.5	0.5	0.7	0.8	0.8	0.8	0.9
150°	0.4	0.4	0.5	0.5	0.6	0.6	0.7	0.8
180°	0.3	0.3	0.4	0.5	0.5	0.5	0.6	0.7

5.0 PERFORMANCE (CONTINUED)

Maximum Axial Distance For 95° Spray Angle in Metric								
Fixed Angle	K-Factor							
	1.7	2.6	3.3	4.6	5.9	7.1	8.1	10.4
0°	4.5	4.6	4.6	4.6	4.6	4.7	4.8	4.9
30°	2.5	2.6	2.8	2.9	3.1	3.2	3.2	3.4
45°	2.1	2.1	2.2	2.3	2.6	2.7	2.7	3.0
60°	1.6	1.7	1.8	2.0	2.1	2.1	2.3	2.6
90°	1.4	1.4	1.7	1.8	1.8	1.8	1.9	2.1
120°	1.2	1.3	1.4	1.5	1.6	1.7	1.7	1.8
135°	1.1	1.1	1.3	1.4	1.5	1.6	1.6	1.7
150°	1.0	1.1	1.1	1.4	1.4	1.4	1.5	1.6
180°	0.9	1.0	1.0	1.2	1.3	1.3	1.4	1.4


Maximum Axial Distance For 160° Spray Angle in Metric								
Fixed Angle	K-Factor							
	1.7	2.6	3.3	4.6	5.9	7.1	8.1	10.4
0°	1.4	1.4	1.4	1.5	1.5	1.5	1.6	1.6
30°	1.1	1.1	1.2	1.2	1.4	1.4	1.4	1.4
45°	0.9	0.9	1.1	1.1	1.2	1.2	1.2	1.3
60°	0.6	0.6	0.7	0.8	1.0	1.0	1.1	1.1
90°	0.3	0.4	0.5	0.6	0.8	0.8	0.8	0.8
120°	NR	0.3	0.5	0.5	0.6	0.7	0.7	0.8
135°	NR	NR	0.3	0.5	0.5	0.5	0.5	0.6
150°	NR	NR	NR	0.3	0.4	0.4	0.4	0.5
180°	NR	NR	NR	0.3	0.3	0.3	0.4	0.5

Maximum Axial Distance For 110° Spray Angle in Metric								
Fixed Angle	K-Factor							
	1.7	2.6	3.3	4.6	5.9	7.1	8.1	10.4
0°	2.9	3.0	3.0	3.0	3.0	3.2	3.3	3.4
30°	2.0	2.1	2.2	2.4	2.6	2.7	2.7	2.9
45°	1.7	1.8	2.1	2.1	2.3	2.4	2.5	2.6
60°	1.4	1.5	1.7	1.8	1.9	2.1	2.2	2.4
90°	1.1	1.2	1.4	1.4	1.6	1.7	1.8	1.9
120°	1.0	1.1	1.2	1.3	1.4	1.4	1.4	1.6
135°	0.8	0.9	1.1	1.2	1.3	1.3	1.4	1.4
150°	0.8	0.8	1.0	1.1	1.2	1.3	1.3	1.4
180°	0.7	0.8	0.9	1.0	1.1	1.1	1.2	1.3

Maximum Axial Distance For 180° Spray Angle in Metric								
Fixed Angle	K-Factor							
	1.7	2.6	3.3	4.6	5.9	7.1	8.1	10.4
0°	1.0	1.0	1.0	1.1	1.1	1.1	1.1	1.1
30°	0.7	0.7	0.8	0.8	0.9	1.0	1.0	1.0
45°	0.6	0.6	0.7	0.8	0.8	0.9	0.9	0.9
60°	0.5	0.5	0.5	0.6	0.7	0.7	0.8	0.8
90°	NR	NR	0.3	0.3	0.5	0.5	0.5	0.7
120°	NR	NR	0.3	0.3	0.4	0.5	0.5	0.5
135°	NR	NR	NR	0.3	0.3	0.4	0.4	0.5
150°	NR	NR	NR	NR	0.3	0.3	0.4	0.4
180°	NR	NR	NR	NR	NR	0.3	0.3	0.3

6.0 NOTIFICATIONS

⚠ WARNING



- Read and understand all instructions before attempting to install any Victaulic products.
- Always verify that the piping system has been completely depressurized and drained immediately prior to installation, removal, adjustment, or maintenance of any Victaulic products.
- Wear safety glasses, hardhat, and foot protection.

Failure to follow these instructions could result in death or serious personal injury and property damage.

- These products shall be used only in fire protection systems that are designed and installed in accordance with current, applicable National Fire Protection Association (NFPA 13, 13D, 13R, etc.) standards, or equivalent standards, and in accordance with applicable building and fire codes. These standards and codes contain important information regarding protection of systems from freezing temperatures, corrosion, mechanical damage, etc.
- The installer shall understand the use of this product and why it was specified for the particular application.
- The installer shall understand common industry safety standards and potential consequences of improper product installation.
- It is the system designer's responsibility to verify suitability of materials for use with the intended fluid media within the piping system and external environment.
- The material specifier shall evaluate the effect of chemical composition, pH level, operating temperature, chloride level, oxygen level, and flow rate on materials to confirm system life will be acceptable for the intended service.

Failure to follow installation requirements and local and national codes and standards could compromise system integrity or cause system failure, resulting in death or serious personal injury and property damage.

7.0 REFERENCE MATERIALS

[I-40: Victaulic FireLock™ Automatic Sprinklers Installation and Maintenance Instructions](#)

User Responsibility for Product Selection and Suitability

Each user bears final responsibility for making a determination as to the suitability of Victaulic products for a particular end-use application, in accordance with industry standards and project specifications, as well as Victaulic performance, maintenance, safety, and warning instructions. Nothing in this or any other document, nor any verbal recommendation, advice, or opinion from any Victaulic employee, shall be deemed to alter, vary, supersede, or waive any provision of Victaulic Company's standard conditions of sale, installation guide, or this disclaimer.

Intellectual Property Rights

No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidiaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

Installation

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at www.victaulic.com.

Warranty

Refer to the Warranty section of the current Price List or contact Victaulic for details.

Trademarks

Victaulic and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries.